

Feature	ASE (CP-64-15)			UTAC (CP-64-23)			Remarks
	Min	Nom	Max	Min	Nom	Max	
A (Pkg height)	0.70	0.75	0.80	0.70	0.75	0.80	Same
A1(Stand-off)		0.02	0.05		0.02	0.05	Same
A3(LF thickness)	0.203 REF			0.203 REF			Same
D (Body width)	8.90	9.00	9.10	8.90	9.00	9.10	Same
E (Body length)	8.90	9.00	9.10	8.90	9.00	9.10	Same
D2 (Exposed pad width)	7.50	7.60	7.70	7.40	7.50	7.60	New site UT2 exposed pad size is smaller
E2 (Exposed pad length)	7.50	7.60	7.70	7.40	7.50	7.60	New site UT2 exposed pad size is smaller
b (Lead width)	0.18	0.25	0.30	0.20	0.25	0.30	same nominal value
e (Lead pitch)	0.50 BSC			0.50 BSC			same
L (Lead length)	0.35	0.40	0.45	0.30	0.40	0.50	same nominal value

