



TOP VIEW




SIDE VIEW

COMMON DIMENSIONS	
A	0.64 ±0.05
A1	0.19 ±0.03
A2	0.45 REF
b	Ø 0.27 ±0.03
D1	0.40 BASIC
E1	0.80 BASIC
e	0.40 BASIC
SD	0.20 BASIC
SE	0.00 BASIC
DEPOPULATED BUMPS: NONE	



FRONT VIEW

PKG. CODE	E	D	A3
W60A1+1	1.248 ±0.025	0.848 ±0.025	0.040 BASIC
W61F1+1	1.318 ±0.025	0.998 ±0.025	0.025 BASIC



BOTTOM VIEW

NOTES:

1. Terminal pitch is defined by terminal center to center value.
2. Outer dimension is defined by center lines between scribe lines.
3. All dimensions in millimeter.
4. Marking shown is for package orientation reference only.
5. Tolerance is ± 0.02 unless specified otherwise.
6. All dimensions apply to PbFree (+) package codes only.
7. Front - side finish can be either Black or Clear.

- DRAWING NOT TO SCALE -



TITLE PACKAGE OUTLINE 6 BUMPS WLP PKG. 0.4 mm PITCH			
APPROVAL	DOCUMENT CONTROL NO. 21-0656	REV. D	1/1