



| SIZE | QTY | SYM | PLATED | TOL |
|------|-----|----------------|--------|--------|
| 0.3 | 155 | X | YES | +/- |
| 0.9 | 4 | + ^A | YES | +/-0.1 |
| 1.1 | 44 | + ^B | NO | +/-0.1 |
| 1.1 | 22 | + ^B | YES | +/-0.1 |
| 1.5 | 8 | + ^C | YES | +/-0.1 |
| 1.8 | 2 | □ | NO | +/-0.1 |
| 3.2 | 4 | ⊠ | YES | +/-0.1 |