


Symbol	Hit Count	Finished Hole Size	Plated	Hole Type	Rout Path Length	Physical Length
□	334	10.00mil <0.254mm>	PTH	Round		
▽	49	15.00mil <0.381mm>	PTH	Round		
○	50	20.00mil <0.508mm>	PTH	Round		
	433 Total					

NOTES: (UNLESS OTHERWISE SPECIFIED)

- 1) FINISHED BOARD THICKNESS TO BE 42 MILS +/- 10%.
- 2) SOLDERMASK TO BE LPI, COLOR : GREEN, BOTH SIDES.
- 3) PLATING: IMMERSION GOLD OVER ELECTROLESS NICKEL.
- ALL LAYERS USE 1 OZ COPPER.
- 4) SILKSCREEN: TOP SIDE, COLOR: WHITE
- 5) SEE DRILL CHART FOR FINISHED HOLE SIZES.
- 6) HOLE TOLERANCE IS +/- 3 MILS UNLESS OTHERWISE SPECIFIED.
- 7) THIS IS A 4 LAYER BOARD.
- 8) TRACE WIDTHS IN ARTWORK ARE FINISHED SIZES. DO NOT DEVIATE WITHOUT PRIOR AUTHORIZATION FROM SCINTERA.
- 9) BOW AND TWIST: .75% MAX ALLOWABLE.
- 10) FABRICATE PER IPC-6012 CLASS 2 (LATEST REVISION) UNLESS OTHERWISE SPECIFIED.
- 11) REMOVE ALL BURRS AND SHARP EDGES.
- 12) VENDOR SHALL PERFORM FULL NETS LIST TEST - EXTRACT NETS LIST FROM GERBER.
- 13) FINISHED BOARD SHALL BE RoHS COMPLIANT.
- 14) COPPER TO THE EDGE BY DESIGN. NO RELIEF.
- 15) REMOVE UNUSED PADS.
- 16) TENT ALL 10 MIL VIAS USING SOLDERMASK ON THE LAYER4.



ALL PROCESSES MUST BE ROHS COMPLIANT.




CAUTION

THIS ASSEMBLY INCORPORATES
STATIC SENSITIVE DEVICES

ASSEMBLY AND HANDLING MUST BE DONE AT AN
APPROVED STATIC FREE STATION

CAUTION



ASSY TOP