


# POWER SOLUTIONS FOR PRECISION TECHNOLOGY SIGNAL CHAINS

## PRECISION LOW POWER Single-Channel, Differential Input, 16 Bits

Rev. 0 | Feb. 2023



©2023 Analog Devices, Inc. All rights reserved.  
Trademarks and registered trademarks are the  
property of their respective owners.

This document is interactive. You can click on any underlined text to navigate through the document.

For the resources:

APPENDIX	<u>Parts Guide</u>
	<u>Power Requirements</u>

Left-click the Parts Guide and Power Requirements to go through the list of power devices and other references.

The Power Components are listed on the Appendix, and you may click on the part to go through its product page online.

PART #	DESCRIPTION
<u>LT3471</u>	Dual 1.3A, 1.2MHz Boost/Inverter in 3mm × 3mm DFN
<u>LT8604</u>	High Efficiency 42V/120mA Synchronous Buck
<u>LT8570-1</u>	Boost/SEPIC/Inverting DC/DC Converter with 65V Switch, Soft-Start and Sync.

For the individual pages:

Left-click the specific signal chain to go through its respective block diagram or power tree.

Non-isolated	<b>POWER RE</b>
<u>1-Channel</u>	
	<b>PARAMETER</b>
	Supply Voltage
	Supply Current
	PSRR


## APPENDIX

## Parts Guide

## USER GUIDE

## Power Requirements

### Single-Channel, Differential Input, 16 Bits



APPENDIX


[Parts Guide](#)

[USER GUIDE](#)

[Power Requirements](#)

Single-Channel, Differential Input, 16 Bits

Non-isolated	Isolated
<a href="#">1.5V Supply</a>	<a href="#">5V Supply</a>
<a href="#">3.7V Supply</a>	
<a href="#">≥ 5.5V Supply</a>	



\* See datasheet for details on core voltage.

### APPENDIX








[Parts Guide](#)
[USER GUIDE](#)
[Single-Channel, Differential Input, 16 Bits](#)

### Power Requirements

Non-isolated	Isolated
1.5V Supply	5V Supply
3.7V Supply	
> 5.5V Supply	

#### REFERENCE

IN **ADR3625** OUT



\* See datasheet for details on core voltage.

APPENDIX


[Parts Guide](#)

[USER GUIDE](#)

[Power Requirements](#)

Single-Channel, Differential Input, 16 Bits

Non-isolated	Isolated
1.5V Supply	5V Supply
3.7V Supply	
> 5.5V Supply	



\* See datasheet for details on core voltage.

Single-Channel, Differential Input, 16 Bits

Non-isolated	Isolated
1.5V Supply	5V Supply
3.7V Supply	
> 5.5V Supply	

PART #	DESCRIPTION
<b><u>MAX77642</u></b>	Ultra Configurable PMIC Featuring 93% Peak Efficiency Single-Inductor, 3-Output Buck-Boost, 1-LDO for Long Battery Life
<b><u>MAXM17225</u></b>	Tiny, 0.4V to 5.5V Input, 300nA IQ, nanoPower Boost Module with True Shutdown
<b><u>MAXM17532</u></b>	4V to 42V, 100mA, Himalaya uSLIC Step-Down Power Module
<b><u>MAX38641</u></b>	Tiny 1.8V to 5.5V Input, 330nA IQ, 700mA nanoPower Buck Converter
<b><u>ADuM5028</u></b>	Low Emission Isolated DC to DC Converter

Non-isolated	Isolated
1.5V Supply	5V Supply
3.7V Supply	
> 5.5V Supply	

POWER REQUIREMENTS

PARAMETER	STAGES	Amplifier		ADC		Reference	Isolation	
	Part #	AD8233		AD4008		ADR3625	ADuM1441	
	Pin	+V <sub>S</sub>	-V <sub>S</sub>	V <sub>DD</sub>	V <sub>IO</sub>	V <sub>IN</sub>	V <sub>DD1</sub>	V <sub>DD2</sub>
Supply Voltage	V	3.4	-	1.8	1.8	3.4	2.5	2.5
Supply Current	mA	0.07	-	1.78	0.36	0.075	0.9	0.9
PSRR	dB	See datasheet (in-amp, op-amp)		66 (1MHz)	101 (1MHz)	64 (100kHz; C <sub>L</sub> =10μF)	-	

- Note 1:** The supply currents indicated are the maximum quiescent current of the supply rails. For overall full load or short circuit current specifications, refer to the datasheets of the signal chain components.
- Note 2:** The supply voltages indicated are the values for typical applications.
- Note 3:** Consult the corresponding datasheets for details on power dissipation if needed.
- Note 4:** The actual supply current requirement shall be multiplied depending on the number of channels on the signal chain.
- Note 5:** For the MCU power requirements, consult the datasheet.