





NOTES

1. REFER TO JEDEC MO-220.
2. COPLANARITY APPLIES TO LEADS, CORNER LEADS AND DIE ATTACH PAD.
3. BAN TO USE THE LEVEL 1 ENVIRONMENT-RELATED SUBSTANCES OF JCET SPECIFICATIONS.
4. FINISH: Cu/EP • Sn8~20s
5. MAXIM PKG CODE : F142A2F-1
6. MATERIAL MUST BE COMPLIANT WITH MAXIM SPECIFICATION 10-0131 FOR SUBSTANCE CONTENT, MUST BE Eu ROHS COMPLIANT WITHOUT EXEMPTION AND PB-FREE.

		SYMBOL	MIN	NOM	MAX
TOTAL THICKNESS		A	0.5	0.55	0.6
STAND OFF		A1	0	0.02	0.05
MOLD THICKNESS		A2	---	0.4	---
L/F THICKNESS		A3	0.152 REF		
LEAD WIDTH		b	0.2	0.25	0.3
		b1	0.25	0.3	0.35
BODY SIZE	X	D	2.5 BSC		
	Y	E	2.5 BSC		
LEAD PITCH		e	0.5 BSC		
		e1	0.65 BSC		
LEAD LENGTH		L	0.25	0.3	0.35
LEAD EDGE TO PACKAGE		L1	0.15 REF		
LEAD EDGE TO LEAD EDGE		k	0.25 REF		
LEAD CENTER TO PACKAGE CENTER		k1	0.25 BSC		
PACKAGE EDGE TOLERANCE		aaa	0.1		
MOLD FLATNESS		ccc	0.1		
COPLANARITY		eee	0.05		
LEAD OFFSET		bbb	0.1		

—DRAWING NOT TO SCALE—



TITLE:
PACKAGE OUTLINE, 14L FC2QFN
2.5x2.5x0.55mm

APPROVAL

DOCUMENT CONTROL NO.
21-100382

REV. A

1/1