

SPECIFICATIONS

ELECTRICAL CHARACTERISTICS

$V_s = \pm 15\text{ V}$, $T_A = 25^\circ\text{C}$, unless otherwise noted.

Table 1.

Parameter	Symbol	Conditions	FROM		TO		Unit
			OP249A Max	OP249F Max	OP249A Max	OP249F Max	
Offset Voltage	V_{OS}	$V_{cm} = 0\text{V}$	0.5	0.7	0.75	0.9	mV
Offset Voltage Temperature Coefficient	TCV_{OS}	$-40^\circ\text{C} < T_A < +85^\circ\text{C}$	-	6	-	12	$\mu\text{V}/^\circ\text{C}$
		$-55^\circ\text{C} < T_A < +125^\circ\text{C}$	5	-	10	-	$\mu\text{V}/^\circ\text{C}$