Technical Notes on using Analog Devices' DSP components and development tools

Phone: (800) ANALOG-D, FAX: (781) 461-3010, EMAIL: dsp.support@analog.com, FTP: ftp.analog.com, WEB: www.analog.com/dsp

## SHARC SHORT WORD DMA

Last Modified: 8/1/00

## Introduction

The DMA Controller of the Analog Devices SHARC® family processors does not automatically dma 16 bit data from an external memory to the SHARC's internal memory, however 16 bit data transfers can still easily be accomplished. The following Engineer to Engineer Note describes the method used to move 16 bit data into the SHARC's internal memory and includes a sample code.

The external port and serial port DMA channels have a packing capability allowing 16 bit data to be packed to 32 bits. The 32 bit packed words can be transferred to internal memory using standard dma. Once the data is safely in internal memory it can be accessed as short word memory. Figure 1 illustrates how short words are organized in normal word space. The least significant short word address is generated by arithmetically shifting the normal word address to the left 1 bit. Arithmetically shifting the normal word address to the left 1 bit and then setting bit 0 to 1 generates the most significant short word address. For example, if the normal word address for a memory location were 0xC000 the short word address would be 0x18000 for the least significant word and 0x18001 for the most significant word.

All of this information can be found in the ADSP-2106x SHARC User's Manual or the

ADSP-21065L SHARC User's Manual. For better understanding please see the chapters on DMA and Memory in your User's Manual.




Figure 1. Short word addresses

```
Listing1: dma.asm
DMA.ASM
                ADSP-21065L EPORT 16/32 bit packing
GGL, Analog Devices, Inc.
                             7/19/00
This code is a simple example of getting 16 bit floating point data from SDRAM packing it to 32 bits
and using dma to get it into internal memory. Once in internal memory, the data is accessed as short
word and operated on and sent back to internal memory.
*/
#define N 4
#include "def210651.h"
.section/DM
               seg dmda;
.VAR dest[N];
/* This is your destination buffer in internal memory which resides in normal word space */
.section/DM seg sdram;
.VAR source[2*N]=0x1111, 0x2222, 0x3333, 0x4444, 0xAAAA, 0xBBBB, 0xCCCC, 0xDDDD;
/* This is the sample 16 bit data from an external sdram */
.section/pm
              seg rth;
/* This is the interrupt vector table */
Reserved 1: rti; nop; nop; nop;
Chip Reset: idle; jump start; nop; nop;
Reserved 2:
              rti; nop; nop; nop;
stack ov:
              rti; nop; nop; nop;
timerhi:
              rti; nop; nop; nop;
Vector:
              rti; nop; nop; nop;
```

IRQ2:

sport0r:

sport1r:

sport0t:

sport1t:

EP0:

Reserved 4:

Reserved 5:

IRQ1: rti; nop; nop; nop; IRQ0: rti; nop; nop; nop;

Reserved 3: rti; nop; nop; nop;

nop; nop; rti; nop;

```
EP1
              rti; nop; nop; nop;
.section/pm
              seg pmco;
                                                                              */
                           start of main routine
start:
              ustat1=937;
                                                        /*refresh rate*/
              dm(SDRDIV)=ustat1;
              ustat1=dm(IOCTL);
                                                 /*mask in SDRAM settings*/
              bit set ustat1 SDPSS|SDBN2|SDBS3|SDTRP3|SDTRAS5|SDCL2|SDPGS256|SDDCK1;
              dm(IOCTL)=ustat1;
                                                 /*initialize sdram*/
              /* enable interrupts here */
                                                 /* enable global interrupts here */
              bit set MODE1 IRPTEN;
              bit set IMASK EP0I; /* enable eport interrupts here */
/* must set up II IM and C register in memory bufffer; then enable the channel with DEN in DMAC */
/* dma channel 8 is external port buffer 0 */
       r0=0; dm(DMAC0)=r0;
                                                        /*clear DMA register*/
       r0 = 1; dm(IMEP0) = r0;
                                   /* set DMA internal memory DMA modifier to 1*/
       dm(EMEP0)=r0;
                                                        /* set DMA external memory DMA
modifier to 1*/
       r0 = N; dm(CEP0) = r0;
                                                 /*set internal count to N */
       r0=2*N; dm(ECEP0)=r0;
                                                 /*set external DMA count to 2N */
       r0=dest; dm(IIEP0) = r0;
                                          /* Write internal index pointer for dest */
                                          /*Write External DMA buffer Index pointer for source */
       r0=source; dm(EIEP0)=r0;
                                                 /* enable DMA channel, master mode, 16/32bit
       r0=0x0241; dm(DMAC0)=r0;
packing */
wait1: idle;
       /* when this dma completes you will have the 16 bit words that were stored in SDRAM
       packed to 32 bit words in external memory */
       /* the ISR only has an RTI in it, so after the dma is complete
       the program flow will continue in the next instruction */
/* find the first address of the data buffer and convert it to short word */
r0=dest;
```

```
r1=ashift r0 by 1; /* arithmetically shifting a normal word address to the left produces the short word
address of the LSW */
/* initialize dags to the short word buffer */
b0=r1;
m0=1;
10=2*N;
/* operate on the short word data and return to short word space */
r0=dm(i0,m0); f0=funpack r0; /* read the short word floating point data to a register and then unpack it
r1=dm(i0,m0); f1=funpack r1;
f2=f0*f1; r2=fpack f2;
                            /* multiply f0 and f1 and then pack it back into a 16 bit floating point word
dm(i0,m0)=r2;/* send the 16 bit result out to memory */
r3=dm(i0,m0);/* read 16 bit fixed point value */
r4=dm(i0,m0);
r5=r3+r4;
                     /* fixed point add */
dm(i0,m0)=r5;/* send 16 bit result out to memory */
wait2: jump wait2;
Listing 2: ADSP21065L.ldf
ARCHITECTURE(ADSP-21065L)
//
// ADSP-21065L Memory Map:
// Internal memory 0x0000 0000 to 0x0007 ffff
//
             0x0000 0000 to 0x0000 00ff IOP Regs
             0x0000 0100 to 0x0000 01ff IOP Regs of Processor ID 001
//
             0x0000 0200 to 0x0000 02ff IOP Regs of Processor ID 002
             0x0000 0300 to 0x0000 07ff Reserved
//
//
       Block 0 0x0000 8000 to 0x0000 9fff Normal Word (32/48) Addresses
            (0x0000 8000 to 0x0000 97ff) 48-bit words
            (0x0000 8000 to 0x0000 9fff) 32-bit words
//
                                     0x0000 A000 to 0x0000 Bfff Reserved
//
```

```
//
       Block 1 0x0000 C000 to 0x0000 Dfff Normal Word (32/48) Addresses
           (0x0000 C000 to 0x0000 Cfff) 48-bit words
//
           (0x0000 C000 to 0x0000 Dfff) 32-bit words
//
                                  0x0000 E000 to 0x0000 ffff Reserved
//
       Block 0 0x0001 0000 to 0x0001 3fff Short Word (16) Addresses
//
//
                                  0x0001 4000 to 0x0001 7fff Reserved
//
       Block 1 0x0001 8000 to 0x0001 Bfff Short Word (16) Addresses
                                  0x0001 C000 to 0x0001 ffff Reserved
//
  External memory 0x0002 0000 to 0x03ff ffff
// External Bank 0 0x0002 0000 to 0x00ff ffff
// External Bank 1 0x0100 0000 to 0x01ff fffff
// External Bank 2 0x0200 0000 to 0x02ff ffff
// External Bank 3 0x0300 0000 to 0x03ff fffff
// This architecture file allocates:
      Internal 256 words of run-time header in memory block 0
//
            16 words of initialization code in memory block 0
//
          3.73K words of C code space in memory block 0
//
           2K words of C PM data space in memory block 0
           4K words of C DM data space in memory block 1
//
          1.25K words of C heap space in memory block 1
//
          2.75K words of C stack space in memory block 1
SEARCH DIR($ADI DSP\21k\lib)
// The lib060.dlb must come before libc.dlb because libc.dlb has some 21020
// specific code and data
$LIBRARIES = lib060.dlb, libc.dlb, libio32.dlb;
// Libraries from the command line are included in COMMAND LINE OBJECTS.
$OBJECTS = $COMMAND LINE OBJECTS;
MEMORY
      seg rth { TYPE(PM RAM) START(0x00008000) END(0x000080ff) WIDTH(48) }
      seg init { TYPE(PM RAM) START(0x00008100) END(0x0000810f) WIDTH(48) }
      seg pmco { TYPE(PM RAM) START(0x00008110) END(0x00008fff) WIDTH(48) }
      seg_pmda { TYPE(PM RAM) START(0x00009800) END(0x00009fff) WIDTH(32) }
      seg dmda { TYPE(DM RAM) START(0x0000C000) END(0x0000Cfff) WIDTH(32) }
      seg heap { TYPE(DM RAM) START(0x0000D000) END(0x0000D4ff) WIDTH(32) }
      seg stak { TYPE(DM RAM) START(0x0000D500) END(0x0000Dfff) WIDTH(32) }
```

```
seg_sdram { TYPE(DM RAM) START(0x3000000) END(0x030ffeff) WIDTH(32) }
}
PROCESSOR p0
  LINK AGAINST( $COMMAND LINE LINK AGAINST)
  OUTPUT ($COMMAND LINE OUTPUT FILE)
  SECTIONS
            // .text output section
            seg rth
                  INPUT SECTIONS( $OBJECTS(seg rth) $LIBRARIES(seg rth))
            } >seg rth
            seg init
                  INPUT SECTIONS( $OBJECTS(seg init) $LIBRARIES(seg init))
            } >seg init
            seg_pmco
                  INPUT SECTIONS( $OBJECTS(seg pmco) $LIBRARIES(seg pmco))
            } >seg pmco
            seg pmda
                  INPUT_SECTIONS( $OBJECTS(seg_pmda) $LIBRARIES(seg_pmda))
            } >seg pmda
            seg dmda
                  INPUT SECTIONS( $OBJECTS(seg dmda) $LIBRARIES(seg dmda))
            } > seg dmda
            seg sdram /*SHT NOBITS if you do not want to initialize SRAM area in executable*/
                  INPUT SECTIONS( $OBJECTS(seg sdram))
            } > seg sdram
```

```
stackseg
{
      // allocate a stack for the application
      ldf_stack_space = .;
      ldf_stack_length = MEMORY_SIZEOF(seg_stak);
} > seg_stak

heap
{
      // allocate a heap for the application
      ldf_heap_space = .;
      ldf_heap_length = MEMORY_SIZEOF(seg_heap);
      ldf_heap_end = ldf_heap_space + ldf_heap_length - 1;
} > seg_heap
}
```