

PRODUCT RELIABILITY REPORT
FOR

DS2761, Rev A2

Dallas Semiconductor

4401 South Beltwood Parkway
Dallas, TX 75244-3292

Prepared by:

Ken Wendel

Ken Wendel
Reliability Engineering Manager
Dallas Semiconductor
4401 South Beltwood Pkwy.
Dallas, TX 75244-3292
Email : ken.wendel@dalsemi.com
ph: 972-371-3726
fax: 972-371-6016
mbl: 214-435-6610

Conclusion:

The following qualification successfully meets the quality and reliability standards required of all Dallas Semiconductor products:

DS2761, Rev A2

In addition, Dallas Semiconductor's continuous reliability monitor program ensures that all outgoing product will continue to meet Maxim's quality and reliability standards. The current status of the reliability monitor program can be viewed at <http://www.maxim-ic.com/TechSupport/dsreliability.html>.

Device Description:

A description of this device can be found in the product data sheet. You can find the product data sheet at http://dbserv.maxim-ic.com/l_datasheet3.cfm.

Reliability Derating:

The Arrhenius model will be used to determine the acceleration factor for failure mechanisms that are temperature accelerated.

$AfT = \exp((Ea/k) * (1/Tu - 1/Ts)) = tu/ts$
AfT = Acceleration factor due to Temperature
tu = Time at use temperature (e.g. 55°C)
ts = Time at stress temperature (e.g. 125°C)
k = Boltzmann's Constant (8.617×10^{-5} eV/°K)
Tu = Temperature at Use (°K)
Ts = Temperature at Stress (°K)
Ea = Activation Energy (e.g. 0.7 eV)

The activation energy of the failure mechanism is derived from either internal studies or industry accepted standards, or activation energy of 0.7eV will be used whenever actual failure mechanisms or their activation energies are unknown. All deratings will be done from the stress ambient temperature to the use ambient temperature.

An exponential model will be used to determine the acceleration factor for failure mechanisms, which are voltage accelerated.

$AfV = \exp(B * (Vs - Vu))$
AfV = Acceleration factor due to Voltage
Vs = Stress Voltage (e.g. 7.0 volts)
Vu = Maximum Operating Voltage (e.g. 5.5 volts)
B = Constant related to failure mechanism type (e.g. 1.0, 2.4, 2.7, etc.)

The Constant, B, related to the failure mechanism is derived from either internal studies or industry accepted standards, or a B of 1.0 will be used whenever actual failure mechanisms or their B are unknown. All deratings will be done from the stress voltage to the maximum operating voltage. Failure rate data from the operating life test is reported using a Chi-Squared statistical model at the 60% or 90% confidence level (Cf).

The failure rate, Fr, is related to the acceleration during life test by:

$Fr = X / (ts * AfV * AfT * N * 2)$
X = Chi-Sq statistical upper limit
N = Life test sample size

Failure Rates are reported in FITs (Failures in Time) or MTTF (Mean Time To Failure). The FIT rate is related to MTTF by:

$$\text{MTTF} = 1/\text{Fr}$$

NOTE: MTTF is frequently used interchangeably with MTBF.

The calculated failure rate for this device/process is:

FAILURE RATE: **MTTF (YRS): 56519** **FITS: 2.0**

The parameters used to calculate this failure rate are as follows:

Cf: 60% **Ea: 0.7** **B: 0** **Tu: 25 °C** **Vu: 5.5 Volts**

The reliability data follows. At the start of this data is the device information. The next section is the detailed reliability data for each stress. The reliability data section includes the latest data available and may contain some generic data. "*" after DATE CODE denotes specific product data.

Device Information:

Process: 8"-D6W-2P2M,HPVt,E2,EPROGVt,TCN1 ALOCOS:GOI
 Passivation: Passivation w/OxyNitride-Nov. 4% PSG
 Die Size: 97 x 108
 Number of Transistors: 31440
 Interconnect: Aluminum / 1% Silicon / 0.5% Copper
 Gate Oxide Thickness: 150 Å

ELECTRICAL CHARACTERIZATION

DESCRIPTION	DATE CODE	CONDITION	READPOINT	QTY	FAILS	FA#
LATCH-UP	0213	JESD78, I-TEST 25C	1 DYS	3	0	
LATCH-UP	0213	JESD78, I-TEST 85C	1 DYS	3	0	
ESD SENSITIVITY	0217	EOS/ESD S5.1 HBM 500 VOLTS	1 PUL'S	3	0	
ESD SENSITIVITY	0217	EOS/ESD S5.1 HBM 1000 VOLTS	1 PUL'S	3	0	
ESD SENSITIVITY	0217	EOS/ESD S5.1 HBM 2000 VOLTS	1 PUL'S	3	0	
ESD SENSITIVITY	0217	EOS/ESD S5.1 HBM 4000 VOLTS	1 PUL'S	3	2	No FA
ESD SENSITIVITY	0217	EOS/ESD S5.1 HBM 8000 VOLTS	1 PUL'S	3	3	No FA
LATCH-UP	0217	JESD78, Vsupply TEST 125C	2 DYS	3	0	
Total:					5	

OPERATING LIFE

DESCRIPTION	DATE CODE	CONDITION	READPOINT	QTY	FAILS	FA#
HIGH VOLTAGE LIFE	0217	125C, 6.0 VOLTS	1000 HRS	80	0	
HIGH TEMP REVERSE BIAS	0330	125C, 5.5 VOLTS	1000 HRS	45	0	
HIGH TEMP REVERSE BIAS	0330	125C, 5.5 VOLTS	1000 HRS	45	0	
HIGH TEMP REVERSE BIAS	0330	125C, 5.5 VOLTS	1000 HRS	45	0	
HIGH TEMP REVERSE BIAS	0416 *	125C, 5.5 VOLTS	1000 HRS	48	0	

HIGH TEMP REVERSE BIAS	0417	*	125C, 5.5 VOLTS	1000	HRS	48	0
HIGH TEMP REVERSE BIAS	0417	*	125C, 5.5 VOLTS	1000	HRS	48	0
HIGH TEMP OP LIFE	0417	*	125C, 5.5 VOLTS	1000	HRS	77	0
HIGH TEMP REVERSE BIAS	0423	*	125C, 5.5 VOLTS	1000	HRS	45	0
Total:							0

W/E ENDURANCE AND DATA RET'N

DESCRIPTION	DATE	CODE	CONDITION	READPOINT	QTY	FAILS	FA#
WRITE CYCLE STRESS	0217		85 C, 6.0 VOLTS	50 KCYS	77	0	
STORAGE LIFE			150C	1000 HRS	77	0	
Total:							0
FAILURE RATE:	MTTF (YRS): 56519		FITS: 2.0				