

11/29/04

PRODUCT RELIABILITY REPORT FOR

DS2482-100, Rev A3

Dallas Semiconductor

4401 South Beltwood Parkway Dallas, TX 75244-3292

Prepared by:

Don Lipps Staff Reliability Engineer Dallas Semiconductor 4401 South Beltwood Pkwy. Dallas, TX 75244-3292 Email : don.lipps@dalsemi.com ph: 972-371-3739 fax: 972-371-6016

Conclusion:

The following qualification successfully meets the quality and reliability standards required of all Dallas Semiconductor products:

```
DS2482-100, Rev A3
```

In addition, Dallas Semiconductor's continuous reliability monitor program ensures that all outgoing product will continue to meet Maxim's quality and reliability standards. The current status of the reliability monitor program can be viewed at http://www.maxim-ic.com/TechSupport /dsreliability.html.

Device Description:

A description of this device can be found in the product data sheet. You can find the product data sheet at http://dbserv.maxim-ic.com/l_datasheet3.cfm.

Reliability Derating:

The Arrhenius model will be used to determine the acceleration factor for failure mechanisms that are temperature accelerated.

AfT = exp((Ea/k)*(1/Tu - 1/Ts)) = tu/ts AfT = Acceleration factor due to Temperature tu = Time at use temperature (e.g. 55°C) ts = Time at stress temperature (e.g. 125°C) k = Boltzmann's Constant (8.617 x 10-5 eV/°K) Tu = Temperature at Use (°K) Ts = Temperature at Stress (°K) Ea = Activation Energy (e.g. 0.7 ev)

The activation energy of the failure mechanism is derived from either internal studies or industry accepted standards, or activation energy of 0.7ev will be used whenever actual failure mechanisms or their activation energies are unknown. All deratings will be done from the stress ambient temperature to the use ambient temperature.

An exponential model will be used to determine the acceleration factor for failure mechanisms, which are voltage accelerated.

AfV = exp(B*(Vs - Vu)) AfV = Acceleration factor due to Voltage Vs = Stress Voltage (e.g. 7.0 volts) Vu = Maximum Operating Voltage (e.g. 5.5 volts) B = Constant related to failure mechanism type (e.g. 1.0, 2.4, 2.7, etc.)

The Constant, B, related to the failure mechanism is derived from either internal studies or industry accepted standards, or a B of 1.0 will be used whenever actual failure mechanisms or their B are unknown. All deratings will be done from the stress voltage to the maximum operating voltage. Failure rate data from the operating life test is reported using a Chi-Squared statistical model at the 60% or 90% confidence level (Cf).

The failure rate, Fr, is related to the acceleration during life test by:

Fr = X/(ts * AfV * AfT * N * 2)X = Chi-Sq statistical upper limit N = Life test sample size Failure Rates are reported in FITs (Failures in Time) or MTTF (Mean Time To Failure). The FIT rate is related to MTTF by:

MTTF = 1/Fr

NOTE: MTTF is frequently used interchangeably with MTBF.

The calculated failure rate for this device/process is:

The parameters used to calculate this failure rate are as follows:

Cf: 60%	Ea: 0.7	B: 0	Tu: 25 °C	Vu: 5.5 Volts
---------	---------	------	-----------	---------------

The reliability data follows. A the start of this data is the device information. The next section is the detailed reliability data for each stress. The reliability data section includes the latest data available and may contain some generic data. "*" after DATE CODE denotes specific product data.

Device Information:

OPERATING LIFE

E6H-2P2M,HPVt,TCZ ALOCOS:GOI
Passivation w/OxyNitride-Nov. 4% PSG
79 x 72
10143
Aluminum / 1% Silicon / 0.5% Copper
150 Å

ELECTRICAL CHARACTERIZATION

DESCRIPTION	DATE COD	E CONDITION	REA	DPOINT	QTY	FAILS	FA#
ESD SENSITIVITY	0442 *	EOS/ESD S5.1 HBM 2000 VOLTS	1	PUL'S	3	0	
ESD SENSITIVITY	0442 *	EOS/ESD S5.1 HBM 4000 VOLTS	1	PUL'S	3	0	
ESD SENSITIVITY	0442 *	EOS/ESD S5.1 HBM 8000 VOLTS	1	PUL'S	3	0	
ESD SENSITIVITY	0442 *	IEC 1000-4-2 CONTACT 2000 VOLTS	10	PUL'S	3	0	
ESD SENSITIVITY	0442 *	IEC 1000-4-2 CONTACT 4000 VOLTS	10	PUL'S	3	0	
ESD SENSITIVITY	0442 *	IEC 1000-4-2 CONTACT 8000 VOLTS	10	PUL'S	3	0	
ESD SENSITIVITY	0442 *	EOS/ESD S5.1 HBM 1000 VOLTS	1	PUL'S	3	0	
ESD SENSITIVITY	0442 *	EOS/ESD S5.1 HBM 2000 VOLTS	1	PUL'S	3	0	
ESD SENSITIVITY	0442 *	EOS/ESD S5.1 HBM 4000 VOLTS	1	PUL'S	3	0	
LATCH-UP	0442 *	JESD78, I-TEST 125C	2	DYS	6	0	
LATCH-UP	0442 *	JESD78, Vsupply TEST 125C	2	DYS	6	0	
				Total:		0	

DESCRIPTION	DATE COI	DECONDITION	READ	POINT QT	Y FAILS	FA#
HIGH VOLTAGE LIFE	0227	125C, 6.0 VOLTS	1000	HRS 77	0	
HIGH VOLTAGE LIFE	0310	125C, 6.0 VOLTS	1000	HRS 80	0 0	
HIGH TEMP OP LIFE	0332	125C, 5.25 VOLTS	1000	HRS 77	0	

FAILURE RATE:	МТ	TF (YRS): 72885	FITS: 1.6		
			-	Fotal:	0
HIGH TEMP OP LIFE	0442 *	125C, 5.5 VOLTS	192	HRS 4	5 0
HIGH TEMP OP LIFE	0440	125C, 3.6 VOLTS	192	HRS 4	5 0
HIGH TEMP OP LIFE	0428	125C, 5.5 VOLTS	1000	HRS 4	5 0
HIGH TEMP OP LIFE	0426	125C, 3.6 VOLTS	1000	HRS 7	7 0
HIGH TEMP OP LIFE	0418	125C, 5.5 VOLTS	1000	HRS 4	5 0
HIGH TEMP OP LIFE	0418	125C, 5.0 VOLTS	1000	HRS 7	7 0
HIGH TEMP OP LIFE	0402	125C, 3.5 VOLTS	1000	HRS 4	5 0
HIGH TEMP OP LIFE	0343	125C, 5.0 VOLTS	1000	HRS 8	0 0