

PRODUCT RELIABILITY REPORT FOR

DS2482-800, Rev A3

Dallas Semiconductor

4401 South Beltwood Parkway Dallas, TX 75244-3292

Prepared by:

Don Lipps Staff Reliability Engineer Dallas Semiconductor 4401 South Beltwood Pkwy. Dallas, TX 75244-3292

Email : don.lipps@dalsemi.com

ph: 972-371-3739 fax: 972-371-6016

Conclusion:

The following qualification successfully meets the quality and reliability standards required of all Dallas Semiconductor products:

In addition, Dallas Semiconductor's continuous reliability monitor program ensures that all outgoing product will continue to meet Maxim's quality and reliability standards. The current status of the reliability monitor program can be viewed at http://www.maxim-ic.com/TechSupport/dsreliability.html.

Device Description:

A description of this device can be found in the product data sheet. You can find the product data sheet at http://dbserv.maxim-ic.com/l_datasheet3.cfm.

Reliability Derating:

The Arrhenius model will be used to determine the acceleration factor for failure mechanisms that are temperature accelerated.

```
AfT = \exp((Ea/k)^*(1/Tu - 1/Ts)) = tu/ts
AfT = Acceleration factor due to Temr
```

AfT = Acceleration factor due to Temperature

tu = Time at use temperature (e.g. 55°C)

ts = Time at stress temperature (e.g. 125°C)

k = Boltzmann's Constant (8.617 x 10-5 eV/°K)

Tu = Temperature at Use (°K)

Ts = Temperature at Stress (°K)

Ea = Activation Energy (e.g. 0.7 ev)

The activation energy of the failure mechanism is derived from either internal studies or industry accepted standards, or activation energy of 0.7ev will be used whenever actual failure mechanisms or their activation energies are unknown. All deratings will be done from the stress ambient temperature to the use ambient temperature.

An exponential model will be used to determine the acceleration factor for failure mechanisms, which are voltage accelerated.

```
AfV = exp(B*(Vs - Vu))
```

AfV = Acceleration factor due to Voltage

Vs = Stress Voltage (e.g. 7.0 volts)

Vu = Maximum Operating Voltage (e.g. 5.5 volts)

B = Constant related to failure mechanism type (e.g. 1.0, 2.4, 2.7, etc.)

The Constant, B, related to the failure mechanism is derived from either internal studies or industry accepted standards, or a B of 1.0 will be used whenever actual failure mechanisms or their B are unknown. All deratings will be done from the stress voltage to the maximum operating voltage. Failure rate data from the operating life test is reported using a Chi-Squared statistical model at the 60% or 90% confidence level (Cf).

The failure rate, Fr, is related to the acceleration during life test by:

```
Fr = X/(ts * AfV * AfT * N * 2)
```

X = Chi-Sq statistical upper limit

N = Life test sample size

Failure Rates are reported in FITs (Failures in Time) or MTTF (Mean Time To Failure). The FIT rate is related to MTTF by:

MTTF = 1/Fr

NOTE: MTTF is frequently used interchangeably with MTBF.

The calculated failure rate for this device/process is:

FAILURE RATE: MTTF (YRS): 109941 FITS: 1.0

The parameters used to calculate this failure rate are as follows:

Cf: 60% Ea: 0.7 B: 0 Tu: 25 °C Vu: 5.5 Volts

The reliability data follows. A the start of this data is the device information. The next section is the detailed reliability data for each stress. The reliability data section includes the latest data available and may contain some generic data. "*" after DATE CODE denotes specific product data.

Device Information:

Process: E6H-2P2M,HPVt,TCZ ALOCOS:GOI Passivation: Passivation w/OxyNitride-Nov. 4% PSG

Die Size: 110 x 78 Number of Transistors: 11895

Interconnect: Aluminum / 1% Silicon / 0.5% Copper

Gate Oxide Thickness: 150 Å

ELECTRICAL	CHARACTERIZATION
ELECTRICAL	CHARACIERIZATION

DESCRIPTION	DATE COD	E CONDITION	REA	DPOINT	QTY	FAILS	FA#
ESD SENSITIVITY	0418	EOS/ESD S5.1 HBM 2000 VOLTS	1	PUL'S	3	0	
ESD SENSITIVITY	0418	EOS/ESD S5.1 HBM 4000 VOLTS	1	PUL'S	3	0	
ESD SENSITIVITY	0418	EOS/ESD S5.1 HBM 8000 VOLTS	1	PUL'S	3	0	
ESD SENSITIVITY	0418	IEC 61000-4-2 CONTACT 2000 VOLTS	10	PUL'S	3	0	
ESD SENSITIVITY	0418	IEC 61000-4-2 CONTACT 4000 VOLTS	10	PUL'S	3	0	
ESD SENSITIVITY	0418	IEC 61000-4-2 CONTACT 8000 VOLTS	10	PUL'S	3	0	
ESD SENSITIVITY	0418	EOS/ESD S5.1 HBM 1000 VOLTS	1	PUL'S	3	0	
ESD SENSITIVITY	0418	EOS/ESD S5.1 HBM 2000 VOLTS	1	PUL'S	3	0	
ESD SENSITIVITY	0418	EOS/ESD S5.1 HBM 4000 VOLTS	1	PUL'S	3	0	
LATCH-UP	0418	JESD78, I-TEST 125C	2	DYS	6	0	
LATCH-UP	0418	JESD78, Vsupply TEST 125C	2	DYS	6	0	
ESD SENSITIVITY	0447 *	EOS/ESD S5.1 HBM 2000 VOLTS	1	PUL'S	3	0	
ESD SENSITIVITY	0447 *	EOS/ESD S5.1 HBM 4000 VOLTS	1	PUL'S	3	0	
ESD SENSITIVITY	0447 *	EOS/ESD S5.1 HBM 8000 VOLTS	1	PUL'S	3	0	
ESD SENSITIVITY	0447 *	IEC 61000-4-2 CONTACT 2000 VOLTS	10	PUL'S	3	0	
ESD SENSITIVITY	0447 *	IEC 61000-4-2 CONTACT 4000 VOLTS	10	PUL'S	3	0	
ESD SENSITIVITY	0447 *	IEC 61000-4-2 CONTACT 8000 VOLTS	10	PUL'S	3	0	

ESD SENSITIVITY	0447 *	EOS/ESD S5.1 HBM 1000 VOLTS		1	PUL'S	3	0	
ESD SENSITIVITY	0447 *	EOS/ESD S5.1 HBM 2000 VOLTS		1	PUL'S	3	0	
ESD SENSITIVITY	0447 *	EOS/ESD S5.1 HBM 4000 VOLTS		1	PUL'S	3	0	
LATCH-UP	0447 *	JESD78, I-TEST 125C		2	DYS	6	0	
LATCH-UP	0447 *	JESD78, Vsupply TEST 125C		2	DYS	6	0	
					Total:		0	
OPERATING LIFE								
DESCRIPTION	DATE COD	E CONDITION		REA	DPOINT	QTY	FAILS	FA#
HIGH VOLTAGE LIFE	0227	125C, 6.0 VOLTS		1000	HRS	77	0	
HIGH VOLTAGE LIFE	0310	125C, 6.0 VOLTS		1000	HRS	80	0	
HIGH TEMP OP LIFE	0332	125C, 5.25 VOLTS		1000	HRS	77	0	
HIGH TEMP OP LIFE	0343	125C, 5.0 VOLTS		1000	HRS	80	0	
HIGH TEMP OP LIFE	0402	125C, 3.5 VOLTS		1000	HRS	45	0	
HIGH TEMP OP LIFE	0411	125C, 5.0 VOLTS		500	HRS	80	0	
HIGH TEMP OP LIFE	0418	125C, 5.0 VOLTS		1000	HRS	77	0	
HIGH TEMP OP LIFE	0418	125C, 5.5 VOLTS		1000	HRS	45	0	
HIGH TEMP OP LIFE	0420	125C, 3.5 VOLTS		1000	HRS	77	0	
HIGH TEMP OP LIFE	0426	125C, 3.6 VOLTS		1000	HRS	77	0	
HIGH TEMP OP LIFE	0428	125C, 5.5 VOLTS		1000	HRS	45	0	
HIGH TEMP OP LIFE	0432	125C, 5.0 VOLTS		500	HRS	80	0	
HIGH TEMP OP LIFE	0440	125C, 3.6 VOLTS		1000	HRS	45	0	
HIGH TEMP OP LIFE	0442	125C, 5.5 VOLTS		1000	HRS	45	0	
HIGH TEMP OP LIFE	0446	125C, 5.25 VOLTS		1000	HRS	77	0	
HIGH TEMP OP LIFE	0506 *	125C, 5.5 VOLTS		192	HRS	45	0	
	_				Total:		0	
FAILURE RATE:	M	ΓΤF (YRS): 109941	FITS:	1.0				