



RELIABILITY REPORT  
FOR  
MAX16025TE+T  
PLASTIC ENCAPSULATED DEVICES

September 25, 2017

**MAXIM INTEGRATED**

160 RIO ROBLES  
SAN JOSE, CA 95134

 Eric Wright Reliability Engineer	 Brian Standley Manager, Reliability
--	--

## Conclusion

The MAX16025TE+T successfully meets the quality and reliability standards required of all Maxim Integrated products. In addition, Maxim Integrated's continuous reliability monitoring program ensures that all outgoing product will continue to meet Maxim Integrated's quality and reliability standards.

## Table of Contents

I. ....Device Description	IV. ....Die Information
II. ....Manufacturing Information	V. ....Quality Assurance Information
III. ....Packaging Information	VI. ....Reliability Evaluation
.....Attachments	

## I. Device Description

### A. General

The MAX16025-MAX16030 are dual-/triple-/quad-voltage monitors and sequencers that are offered in a small TQFN package. These devices offer enormous design flexibility as they allow fixed and adjustable thresholds to be selected through logic inputs and provide sequence timing through small external capacitors. These versatile devices are ideal for use in a wide variety of multivoltage applications. As the voltage at each monitored input exceeds its respective threshold, its corresponding output goes high after a propagation delay or a capacitor-set time delay. When a voltage falls below its threshold, its respective output goes low after a propagation delay. Each detector circuit also includes its own enable input, allowing the power-good outputs to be shut off independently. The independent output for each detector is available with push-pull or open-drain configuration with the open-drain version capable of supporting voltages up to 28V, thereby allowing them to interface to shutdown and enable inputs of various DC-DC regulators. Each detector can operate independently as four separate supervisory circuits or can be daisy-chained to provide controlled power-supply sequencing. The MAX16025-MAX16030 also include a reset function that deasserts only after all of the independently monitored voltages exceed their threshold. The reset timeout is internally fixed or can be adjusted externally. These devices are offered in a 4mm x 4mm TQFN package and are fully specified from -40°C to +125°C.

## II. Manufacturing Information

A. Description/Function:	Dual-/Triple-/Quad-Voltage, Capacitor-Adjustable, Sequencing/Supervisory Circuits
B. Process:	B8
C. Number of Device Transistors:	3653
D. Fabrication Location:	USA
E. Assembly Location:	China, Taiwan, Thailand
F. Date of Initial Production:	April 22, 2006

## III. Packaging Information

A. Package Type:	16-pin TQFN 4x4
B. Lead Frame:	Copper
C. Lead Finish:	100% matte Tin
D. Die Attach:	Conductive
E. Bondwire:	Au (1 mil dia.)
F. Mold Material:	Epoxy with silica filler
G. Assembly Diagram:	#05-9000-2285
H. Flammability Rating:	Class UL94-V0
I. Classification of Moisture Sensitivity per JEDEC standard J-STD-020-C	Level 1
J. Single Layer Theta Ja:	59.3°C/W
K. Single Layer Theta Jc:	5.7°C/W
L. Multi Layer Theta Ja:	40°C/W
M. Multi Layer Theta Jc:	5.7°C/W

## IV. Die Information

A. Dimensions:	80X88 mils
B. Passivation:	Si <sub>3</sub> N <sub>4</sub> /SiO <sub>2</sub> (Silicon nitride/ Silicon dioxide)
C. Interconnect:	Al/0.5%Cu with Ti/TiN Barrier
D. Backside Metallization:	None
E. Minimum Metal Width:	0.8 microns (as drawn)
F. Minimum Metal Spacing:	0.8 microns (as drawn)
G. Isolation Dielectric:	SiO <sub>2</sub>
H. Die Separation Method:	Wafer Saw

## V. Quality Assurance Information

A. Quality Assurance Contacts:	Eric Wright (Reliability Engineering) Brian Standley (Manager, Reliability) Bryan Preeshl (Vice President of QA)
B. Outgoing Inspection Level:	0.1% for all electrical parameters guaranteed by the Datasheet. 0.1% for all Visual Defects.
C. Observed Outgoing Defect Rate:	< 50 ppm
D. Sampling Plan:	Mil-Std-105D

## VI. Reliability Evaluation

### A. Accelerated Life Test

The results of the 135C biased (static) life test are shown in Table 1. Using these results, the Failure Rate ( $\lambda$ ) is calculated as follows:

$$\lambda = \frac{1}{\text{MTTF}} = \frac{1.83}{192 \times 4340 \times 48 \times 2} \quad (\text{Chi square value for MTTF upper limit})$$

(where 4340 = Temperature Acceleration factor assuming an activation energy of 0.8eV)

$$\lambda = 22.9 \times 10^{-9}$$

$$\lambda = 22.9 \text{ F.I.T. (60\% confidence level @ 25°C)}$$

The following failure rate represents data collected from Maxim Integrated's reliability monitor program. Maxim Integrated performs quarterly life test monitors on its processes. This data is published in the Reliability Report found at <http://www.maximintegrated.com/qa/reliability/monitor>. Cumulative monitor data for the B8 Process results in a FIT Rate of 0.06 @ 25C and 0.99 @ 55C (0.8 eV, 60% UCL)

### B. E.S.D. and Latch-Up Testing

The MT01 die type has been found to have all pins able to withstand an HBM transient pulse of <500V per JEDEC JESD22-A114. Latch-Up testing has shown that this device withstands a current of +/-250mA and overvoltage per JEDEC JESD78.

**Table 1**  
Reliability Evaluation Test Results  
**MAX16025TE+T**

TEST ITEM	TEST CONDITION	FAILURE IDENTIFICATION	SAMPLE SIZE	NUMBER OF FAILURES
Static Life Test (Note 1)	Ta = 135C Biased Time = 192 hrs.	DC Parameters & functionality	48	0

Note 1: Life Test Data may represent plastic DIP qualification lots.