

RELIABILITY REPORT FOR MAX1617AMEE+ PLASTIC ENCAPSULATED DEVICES

December 3, 2009

MAXIM INTEGRATED PRODUCTS

120 SAN GABRIEL DR. SUNNYVALE, CA 94086

Approved by
Ken Wendel
Quality Assurance
Director, Reliability Engineering



Conclusion

The MAX1617AMEE+ successfully meets the quality and reliability standards required of all Maxim products. In addition, Maxim's continuous reliability monitoring program ensures that all outgoing product will continue to meet Maxim's quality and reliability standards.

Table of Contents

- I.Device Description V.Quality Assur II.Manufacturing Information VI.Reliability Eva
- III.Packaging Information
-Attachments

V.Quality Assurance Information VI.Reliability Evaluation

I. Device Description

A. General

The MAX1617A (patents pending) is a precise digital thermometer that reports the temperature of both a remote sensor and its own package. The remote sensor is a diode-connected transistor-typically a low-cost, easily mounted 2N3904 NPN type-that replaces conventional thermistors or thermocouples. Remote accuracy is ±3°C for multiple transistor manufacturers, with no calibration needed. The remote channel can also measure the die temperature of other ICs, such as microprocessors, that contain an on-chip, diode-connected transistor. The 2-wire serial interface accepts standard System Management Bus (SMBus™) Write Byte, Read Byte, Send Byte, and Receive Byte commands to program the alarm thresholds and to read temperature data. The data format is 7 bits plus sign, with each bit corresponding to 1°C, in two's complement format. Measurements can be done automatically and autonomously, with the conversion rate programmed by the user or programmed to operate in a single-shot mode. The adjustable rate allows the user to control the supply-current drain. The MAX1617A is nearly identical to the popular MAX1617, but has improved SMBus timing specifications, improved bus collision immunity, software manufacturer and device identification available via the serial interface, and a power-on reset function that can force a reset of the slave address via the serial interface.



II. Manufacturing Information

Remote/Local Temperature Sensor with SMBus Serial Interface

B12

Pre 1997

Oregon, California or Texas

Malaysia, Philippines, Thailand

- A. Description/Function:
- B. Process:
- C. Number of Device Transistors:
- D. Fabrication Location:
- E. Assembly Location:
- F. Date of Initial Production:

III. Packaging Information

A. Package Type:	16-pin QSOP
B. Lead Frame:	Copper
C. Lead Finish:	100% matte Tin
D. Die Attach:	Conductive
E. Bondwire:	Au (1.3 mil dia.)
F. Mold Material:	Epoxy with silica filler
G. Assembly Diagram:	#05-2301-0004
H. Flammability Rating:	Class UL94-V0
 Classification of Moisture Sensitivity per JEDEC standard J-STD-020-C 	Level 1
J. Single Layer Theta Ja:	120°C/W
K. Single Layer Theta Jc:	37°C/W
L. Multi Layer Theta Ja:	103.7°C/W
M. Multi Layer Theta Jc:	37°C/W

IV. Die Information

Α.	Dimensions:	86 X 116 mils
В.	Passivation:	Si_3N_4/SiO_2 (Silicon nitride/ Silicon dioxide)
C.	Interconnect:	Al/0.5%Cu with Ti/TiN Barrier
D.	Backside Metallization:	None
E.	Minimum Metal Width:	1.2 microns (as drawn)
F.	Minimum Metal Spacing:	1.2 microns (as drawn)
G.	Bondpad Dimensions:	5 mil. Sq.
Н.	Isolation Dielectric:	SiO ₂
I.	Die Separation Method:	Wafer Saw



V. Quality Assurance Information

A.	Quality Assurance Contacts:	Ken Wendel (Director, Reliability Engineering)		
		Bryan Preeshl (Managing Director of QA)		
В.	Outgoing Inspection Level:	0.1% for all electrical parameters guaranteed by the Datasheet.		
		0.1% For all Visual Defects.		
C.	Observed Outgoing Defect Rate:	< 50 ppm		
D.	Sampling Plan:	Mil-Std-105D		

VI. Reliability Evaluation

A. Accelerated Life Test

The results of the 135°C biased (static) life test are shown in Table 1. Using these results, the Failure Rate (λ) is calculated as follows:

 $\lambda = \underbrace{1}_{\text{MTTF}} = \underbrace{1.83}_{192 \times 4340 \times 553 \times 2} \text{ (Chi square value for MTTF upper limit)}$ $\lambda = 1.94 \times 10^{-9}$ $\lambda = 1.94 \text{ F.I.T. (60\% confidence level @ 25°C)}$

The following failure rate represents data collected from Maxim"s reliability monitor program. Maxim performs quarterly life test monitors on its processes. This data is published in the Reliability Report found at http://www.maxim-ic.com/qa/reliability/monitor. Cumulative monitor data for the B12 Process results in a FIT Rate of 0.06 @ 25C and 1.06 @ 55C (0.8 eV, 60% UCL)

B. Moisture Resistance Tests

The industry standard 85°C/85%RH or HAST testing is monitored per device process once a quarter.

C. E.S.D. and Latch-Up Testing

The PY09 die type has been found to have all pins able to withstand a HBM transient pulse of +/-2500 V per Mil-Std 883 Method 3015.7. Latch-Up testing has shown that this device withstands a current of +/-250 mA.



Table 1 Reliability Evaluation Test Results

MAX1617AMEE+

	FAILURE	SAMPLE SIZE	NUMBER OF FAILURES				
Static Life Test (Note 1)							
a = 135°C	DC Parameters	553	0				
ased	& functionality						
me = 192 hrs.							
Moisture Testing (Note 2)							
a = 130°C	DC Parameters	77	0				
H = 85%	& functionality						
ased							
me = 96hrs.							
Mechanical Stress (Note 2)							
5°C/150°C	DC Parameters	77	0				
000 Cycles	& functionality						
ethod 1010							
a = r - 2 = a + a = r - 2 = a = r - 2 = a = r - 2 = a = r -	= 135°C ased ne = 192 hrs.) = 130°C 1 = 85% ased ne = 96hrs. 2) 5°C/150°C 00 Cycles ethod 1010	IDENTIFICATION = 135°C DC Parameters & functionality ased & functionality ne = 192 hrs. DC Parameters 1 = 85% & functionality ased w functionality ne = 96hrs. DC Parameters 2) 5°C/150°C DC Parameters 00 Cycles & functionality athor 1010 C	IDENTIFICATION = 135°C DC Parameters 553 ased & functionality ne = 192 hrs. DC Parameters 77 1 = 85% & functionality 77 4 = 85% & functionality 77 ased				

Note 1: Life Test Data may represent plastic DIP qualification lots.

Note 2: Generic Package/Process data