

11/12/2015



**PRODUCT RELIABILITY REPORT  
FOR**

**MAX35102**

**Maxim Integrated**

**14460 Maxim Dr.  
Dallas, TX 75244**

**Approved by:**

**Sokhom Chum  
Sr. Member of Technical Staff,  
Reliability Engineering**

**Conclusion:**

The following qualification successfully meets the quality and reliability standards required of all Maxim Integrated products:

MAX35102

In addition, Maxim Integrated's continuous reliability monitor program ensures that all outgoing product will continue to meet Maxim's quality and reliability standards. The current status of the reliability monitor program can be viewed at <http://www.maximintegrated.com/qa/reliability/monitor>.

**Device Description:**

A description of this device can be found in the product data sheet. You can find the product data sheet at <http://www.maximintegrated.com/search/partsmvp>.

**Reliability Derating:**

The Arrhenius model will be used to determine the acceleration factor for failure mechanisms that are temperature accelerated.

$AfT = \exp((Ea/k)(1/T_u - 1/T_s)) = tu/ts$   
AfT = Acceleration factor due to Temperature  
tu = Time at use temperature (e.g. 55°C)  
ts = Time at stress temperature (e.g. 125°C)  
k = Boltzmann's Constant ( $8.617 \times 10^{-5} \text{ eV}/\text{K}$ )  
Tu = Temperature at Use (°K)  
Ts = Temperature at Stress (°K)  
Ea = Activation Energy (e.g. 0.7 ev)

The activation energy of the failure mechanism is derived from either internal studies or industry accepted standards, or activation energy of 0.7ev will be used whenever actual failure mechanisms or their activation energies are unknown. All deratings will be done from the stress ambient temperature to the use ambient temperature.

An exponential model will be used to determine the acceleration factor for failure mechanisms, which are voltage accelerated.

$AfV = \exp(B(V_s - V_u))$   
AfV = Acceleration factor due to Voltage  
Vs = Stress Voltage (e.g. 7.0 volts)  
Vu = Maximum Operating Voltage (e.g. 5.5 volts)  
B = Constant related to failure mechanism type (e.g. 1.0, 2.4, 2.7, etc.)

The Constant, B, related to the failure mechanism is derived from either internal studies or industry accepted standards, or a B of 1.0 will be used whenever actual failure mechanisms or their B are unknown. All deratings will be done from the stress voltage to the maximum operating voltage. Failure rate data from the operating life test is reported using a Chi-Squared statistical model at the 60% or 90% confidence level (Cf).

The failure rate, Fr, is related to the acceleration during life test by:

$Fr = X/(ts * AfV * AfT * N * 2)$   
X = Chi-Sq statistical upper limit  
N = Life test sample size

Failure Rates are reported in FITs (Failures in Time) or MTTF (Mean Time To Failure). The FIT rate is related to MTTF by:

$$\text{MTTF} = 1/\text{Fr}$$

NOTE: MTTF is frequently used interchangeably with MTBF.

The calculated failure rate for this device/process is:

<b>FAILURE RATE:</b>	<b>MTTF (YRS):</b>	<b>148536</b>	<b>FITS:</b>	<b>0.8</b>
	<b>DEVICE HOURS:</b>	<b>1192254440</b>	<b>FAILS:</b>	<b>0</b>

Only data from Operating Life or similar stresses are used for this calculation.

The parameters used to calculate this failure rate are as follows:

<b>Cf: 60%</b>	<b>Ea: 0.7</b>	<b>B: 0</b>	<b>Tu: 25 °C</b>	<b>Vu: 3.6 Volts</b>
----------------	----------------	-------------	------------------	----------------------

The reliability data follows. At the start of this data is the device information. The next section is the detailed reliability data for each stress. The reliability data section includes the latest data available and may contain some generic data. **Bold** Product Number denotes specific product data.

#### Device Information:

Process:	TSMC 0.18um Mixed signal, Embedded Flash, General Purpose
Passivation:	SiO/SiN
Die Size:	78 x 84
Number of Transistors:	177011
Interconnect:	Aluminum / 0.5% Copper
Gate Oxide Thickness:	32 Å

#### ESD HBM

DESCRIPTION	DATE CODE/PRODUCT/LOT	CONDITION	READPOIN	QTY	FAILS	FA#
ESD SENSITIVITY	1352 <b>MAX35101</b>	ZK146209DC JESD22-A114 HBM 500 VOLTS	1	PUL'S	5	0
ESD SENSITIVITY	1352 <b>MAX35101</b>	ZK146209DC JESD22-A114 HBM 1000 VOLTS	1	PUL'S	5	0
ESD SENSITIVITY	1352 <b>MAX35101</b>	ZK146209DC JESD22-A114 HBM 1500 VOLTS	1	PUL'S	5	0
ESD SENSITIVITY	1352 <b>MAX35101</b>	ZK146209DC JESD22-A114 HBM 2000 VOLTS	1	PUL'S	5	0
ESD SENSITIVITY	1352 <b>MAX35101</b>	ZK146209DC JESD22-A114 HBM 2500 VOLTS	1	PUL'S	5	0
<b>Total:</b>						<b>0</b>

#### LATCH-UP

DESCRIPTION	DATE CODE/PRODUCT/LOT	CONDITION	READPOIN	QTY	FAILS	FA#
LATCH-UP I	1352 <b>MAX35101</b>	ZK146209DC JESD78A, I-TEST 25C 100mA			6	0
LATCH-UP I	1352 <b>MAX35101</b>	ZK146209DC JESD78A, I-TEST 25C 250mA			6	0
LATCH-UP V	1352 <b>MAX35101</b>	ZK146209DC JESD78A, V-SUPPLY TEST 25C			6	0
<b>Total:</b>						<b>0</b>

---

**OPERATING LIFE**

DESCRIPTION	DATE CODE/PRODUCT/LOT	CONDITION	READPOIN	QTY	FAILS	FA#
HIGH TEMP OP LIFE	0814 MAXQ1103	QN089294A 125C, 3.6V (PSA) & 2.0V (PSB)	1000 HRS	77	0	
HIGH TEMP OP LIFE	0828 MAXQ2010	QK086138C 125C, 3.6 VOLTS	1000 HRS	76	0	
HIGH TEMP OP LIFE	0837 MAX2990	QN096322A 125C, 3.6V (PSA) & 2.0V (PSB)	1000 HRS	77	0	
HIGH TEMP OP LIFE	0851 MAXQ3108	QJ091011AC 125C, 3.6 VOLTS	192 HRS	73	0	
HIGH TEMP OP LIFE	0851 MAXQ610	QJ091123AB 125C, 3.6V (PSA) & 2.0V (PSB)	1000 HRS	77	0	
HIGH TEMP OP LIFE	0852 MAXQ1850	QJ091074AA 125C, 3.6 VOLTS	192 HRS	75	0	
HIGH TEMP OP LIFE	0909 MAXQ8913	NQQ8ZAD 125C, 3.6V (PSA) & 5.0V (PSB)	192 HRS	77	0	
HIGH TEMP OP LIFE	0934 MAXQ1103	QN101437A 125C, 3.6V (PSA) & 2.0V (PSB)	192 HRS	77	0	
HIGH TEMP OP LIFE	0946 MAXQ622	QN091481C 125C, 3.6V (PSA) & 5.5V (PSB)	192 HRS	77	0	
HIGH TEMP OP LIFE	1006 MAXQ1004	QS101775AB 125C, 3.6V (PSA) & 5.0V (PSB)	192 HRS	45	0	
HIGH TEMP OP LIFE	1024 MAXQ1010	QJ101790AG 125C, 5.5V (PS1) & 3.6V (PS2)	192 HRS	45	0	
HIGH TEMP OP LIFE	1024 MAX31782	QJ102013AC 125C, 5.5 VOLTS	192 HRS	45	0	
HIGH TEMP OP LIFE	1030 MAXQ613	QJ101861CH 135C, 3.6 V (PSA)	192 HRS	45	0	
HIGH TEMP OP LIFE	1050 MAXQ6831	ZN112250BC 125C, 3.6V (PSA), 1.89V (PSB) & 2.94V (PSD)	1000 HRS	48	0	
HIGH TEMP OP LIFE	1111 MAXQ618	ZJ112624AD 125C, 3.6 VOLTS	192 HRS	48	0	
HIGH TEMP OP LIFE	1119 MAXQ1740	ZJ112746BA 125C, 3.6 VOLTS	192 HRS	48	0	
HIGH TEMP OP LIFE	1120 DS4830	ZS112802AC 125C, 3.3 VOLTS	192 HRS	77	0	
HIGH TEMP OP LIFE	1134 MAXQ1050	ZS123062AB 125C, 5.5V (PSA) & 3.6V (PSB)	192 HRS	48	0	
HIGH TEMP OP LIFE	1135 MAXQ610	ZJ111435FC- 125C, 3.6V (PSA) & 2.0V (PSB)	1000 HRS	77	0	
HIGH TEMP OP LIFE	1135 MAXQ610	ZJ111435BD 125C, 3.6V (PSA) & 2.0V (PSB)	1000 HRS	77	0	
HIGH TEMP OP LIFE	1135 MAXQ610	ZJ111438BB- 125C, 3.6V (PSA) & 2.0V (PSB)	1000 HRS	77	0	
HIGH TEMP OP LIFE	1211 MAXQ615	ZS123275AE 125C, 3.6 VOLTS	192 HRS	80	0	
HIGH TEMP OP LIFE	1219 MAX34451	ZJ133319BC 125C, 3.6 VOLTS	192 HRS	80	0	
HIGH TEMP OP LIFE	1223 MAXQ1011	GW123374A 125C, 5.5V (PS1) & 3.6V (PS2)	1000 HRS	48	0	

---

HIGH TEMP OP LIFE	1242	MAXQ305	ZJ133525BB 125C, 3.3V (PSA), 1.5V (PSB)	192	HRS	80	0
HIGH TEMP OP LIFE	1246	MAXQ1741	ZS133574BB 125C, 3.6 VOLTS	192	HRS	48	0
HIGH TEMP OP LIFE	1310	MAXQ610	ZX133775AC 125C, 3.6 VOLTS	1000	HRS	48	0
HIGH TEMP OP LIFE	1310	MAXQ610	ZX133775AD 125C, 3.6 VOLTS	1000	HRS	48	0
HIGH TEMP OP LIFE	1310	MAXQ610	ZX133775AE 125C, 3.6 VOLTS	1000	HRS	48	0
HIGH TEMP OP LIFE	1310	MAXQ149	ZX133838AB 125C, 3.6V (PSB) & 5.5V (PSA)	192	HRS	80	0
HIGH TEMP OP LIFE	1315	MAXQ1851	ZX133763BB 125C, 3.6 VOLTS	192	HRS	80	0
HIGH TEMP OP LIFE	1317	MAXQ616	ZX133909CA 125C, 3.6 VOLTS	192	HRS	48	0
HIGH TEMP OP LIFE	1317	MAXQ616	ZX133909CA 125C, 3.6 VOLTS	192	HRS	32	0
HIGH TEMP OP LIFE	1317	MAX34462	ZK133919AC 125C, 3.6 VOLTS	264	HRS	80	0
HIGH TEMP OP LIFE	1317	MAX34462	GK133919A 125C, 3.6 VOLTS	1000	HRS	80	0
HIGH TEMP OP LIFE	1320	MAXQ1852	ZJ136012AB 125C, 3.6V (PSA) & 5.5V (PSB)	192	HRS	80	0
HIGH TEMP OP LIFE	1340	DS4830A	GX146103BB 125C, 3.6 VOLTS	240	HRS	80	0
HIGH TEMP OP LIFE	1344	MAX2906	ZX143837AD 125C, 5.5 VOLTS	408	HRS	79	0
HIGH TEMP OP LIFE	1345	MAXQ617	ZX146356AD 125C, 3.6 VOLTS	192	HRS	48	0
HIGH TEMP OP LIFE	1345	MAXQ617	ZX146356AD 125C, 3.6 VOLTS	192	HRS	32	0
HIGH TEMP OP LIFE	1352	<b>MAX35101</b>	ZK146209DC 125C, 3.6 VOLTS	192	HRS	80	0
HIGH TEMP OP LIFE	1407	MAXQ610	ZS143384CB 125C, 3.6V (PSA) & 2.0V (PSB)	192	HRS	80	0
HIGH TEMP OP LIFE	1407	MAXQ610	ZS143369EB 125C, 3.6V (PSA) & 2.0V (PSB)	192	HRS	80	0
						Total:	<b>0</b>
<b>FAILURE RATE:</b>		<b>MTTF (YRS):</b>	<b>148536</b>	<b>FITS:</b>		<b>0.8</b>	
		<b>DEVICE HOURS:</b>	<b>1192254440</b>	<b>FAILS:</b>		<b>0</b>	

MAX35102 is built with the identical die of MAX35101.