

RELIABILITY REPORT
FOR
MAX5463EXK
PLASTIC ENCAPSULATED DEVICES

August 5, 2003

MAXIM INTEGRATED PRODUCTS

120 SAN GABRIEL DR.

SUNNYVALE, CA 94086

Written by



Jim Pedicord
Quality Assurance
Reliability Lab Manager

Reviewed by



Bryan J. Preeshl
Quality Assurance
Executive Director

Conclusion

The MAX5463 successfully meets the quality and reliability standards required of all Maxim products. In addition, Maxim's continuous reliability monitoring program ensures that all outgoing product will continue to meet Maxim's quality and reliability standards.

Table of Contents

| | |
|-----------------------------------|--------------------------------------|
| I.Device Description | V.Quality Assurance Information |
| II.Manufacturing Information | VI.Reliability Evaluation |
| III.Packaging Information | IV.Die Information |
| |Attachments |

I. Device Description

A. General

The MAX5463 linear-taper digital potentiometer performs the same function as a mechanical potentiometer or a variable resistor. This device consists of a fixed resistor and a wiper contact with 32-tap points that are digitally controlled through a 2-wire serial interface.

The 50k Ω MAX5463 is available in a space-saving 5-pin SC70 packages.

B. Absolute Maximum Ratings

| <u>Item</u> | <u>Rating</u> |
|---|-----------------------|
| VDD to GND | -0.3V to +6V |
| All Other Pins to GND | -0.3V to (VDD + 0.3)V |
| Input and Output Latch-Up Immunity | $\pm 200\text{mA}$ |
| Maximum Continuous Current into H, L, and W | $\pm 0.6\text{mA}$ |
| Operating Temperature Range | -40°C to +85°C |
| Junction Temperature | +150°C |
| Storage Temperature Range | -65°C to +150°C |
| Soldering Temperature (soldering, 10s) | +300°C |
| Continuous Power Dissipation (TA = +70°C) | |
| 5-Pin SC70 | 247mW |
| Derates above +70°C | |
| 5-Pin SC70 | 3.1mW/°C |

II. Manufacturing Information

| | |
|----------------------------------|--|
| A. Description/Function: | 32-Tap FleaPoT™, 2-Wire Digital Potentiometers |
| B. Process: | S6 (Standard 0.6 micron silicon gate CMOS) |
| C. Number of Device Transistors: | 792 |
| D. Fabrication Location: | California, USA |
| E. Assembly Location: | Malaysia or Thailand |
| F. Date of Initial Production: | April, 2001 |

III. Packaging Information

| | |
|---|--------------------------|
| A. Package Type: | 5-Pin SC70 |
| B. Lead Frame: | Alloy 42 or Copper |
| C. Lead Finish: | Solder Plate |
| D. Die Attach: | Non-Conductive Epoxy |
| E. Bondwire: | Gold (1 mil dia.) |
| F. Mold Material: | Epoxy with silica filler |
| G. Assembly Diagram: | #05-3401-0001 |
| H. Flammability Rating: | Class UL94-V0 |
| I. Classification of Moisture Sensitivity per JEDEC standard JESD22-112: | Level 1 |

IV. Die Information

| | |
|----------------------------|---|
| A. Dimensions: | 31 x 30 mils |
| B. Passivation: | Si ₃ N ₄ /SiO ₂ (Silicon nitride/ Silicon dioxide) |
| C. Interconnect: | Aluminum/Si (Si = 1%) |
| D. Backside Metallization: | None |
| E. Minimum Metal Width: | 0.6 microns (as drawn) |
| F. Minimum Metal Spacing: | 0.6 microns (as drawn) |
| G. Bondpad Dimensions: | 5 mil. Sq. |
| H. Isolation Dielectric: | SiO ₂ |
| I. Die Separation Method: | Wafer Saw |

V. Quality Assurance Information

- A. Quality Assurance Contacts: Jim Pedicord (Manager, Reliability Operations)
Bryan Preeshl (Executive Director)
Kenneth Huening (Vice President)
- B. Outgoing Inspection Level: 0.1% for all electrical parameters guaranteed by the Datasheet.
0.1% For all Visual Defects.
- C. Observed Outgoing Defect Rate: < 50 ppm
- D. Sampling Plan: Mil-Std-105D

VI. Reliability Evaluation

A. Accelerated Life Test

The results of the 135°C biased (static) life test are shown in **Table 1**. Using these results, the Failure Rate (λ) is calculated as follows:

$$\lambda = \frac{1}{\text{MTTF}} = \frac{1.83}{192 \times 4389 \times 80 \times 2} \quad (\text{Chi square value for MTTF upper limit})$$

↑
Temperature Acceleration factor assuming an activation energy of 0.8eV

$$\lambda = 13.57 \times 10^{-9}$$

$$\lambda = 13.57 \text{ F.I.T. (60\% confidence level @ 25°C)}$$

This low failure rate represents data collected from Maxim's reliability monitor program. In addition to routine production Burn-In, Maxim pulls a sample from every fabrication process three times per week and subjects it to an extended Burn-In prior to shipment to ensure its reliability. The reliability control level for each lot to be shipped as standard product is 59 F.I.T. at a 60% confidence level, which equates to 3 failures in an 80 piece sample. Maxim performs failure analysis on any lot that exceeds this reliability control level. Attached Burn-In Schematic (Spec. # 06-5675) shows the static Burn-In circuit. Maxim also performs quarterly 1000 hour life test monitors. This data is published in the Product Reliability Report (**RR-1M**).

B. Moisture Resistance Tests

Maxim pulls pressure pot samples from every assembly process three times per week. Each lot sample must meet an LTPD = 20 or less before shipment as standard product. Additionally, the industry standard 85°C/85%RH testing is done per generic device/package family once a quarter.

C. E.S.D. and Latch-Up Testing

The DP06-3 die type has been found to have all pins able to withstand a transient pulse of $\pm 2000\text{V}$ per Mil-Std-883 Method 3015 (reference attached ESD Test Circuit). Latch-Up testing has shown that this device withstands a current of $\pm 200\text{mA}$.

Table 1
Reliability Evaluation Test Results

MAX5463EXK

| TEST ITEM | TEST CONDITION | FAILURE IDENTIFICATION | PACKAGE | SAMPLE SIZE | NUMBER OF FAILURES |
|-----------------------------------|---|----------------------------------|---------|-------------|--------------------|
| Static Life Test (Note 1) | | | | | |
| | Ta = 135°C Biased Time = 192 hrs. | DC Parameters & functionality | | 80 | 0 |
| Moisture Testing (Note 2) | | | | | |
| Pressure Pot | Ta = 121°C P = 15 psi. RH= 100% Time = 168hrs. | DC Parameters & functionality | SC70 | 77 | 0 |
| 85/85 | Ta = 85°C RH = 85% Biased Time = 1000hrs. | DC Parameters & functionality | | 77 | 0 |
| Mechanical Stress (Note 2) | | | | | |
| Temperature Cycle | -65°C/150°C 1000 Cycles Method 1010 | DC Parameters & functionality | | 77 | 0 |

Note 1: Life Test Data may represent plastic DIP qualification lots.

Note 2: Generic Package/Process data

Attachment #1

TABLE II. Pin combination to be tested. 1/ 2/

| | Terminal A (Each pin individually connected to terminal A with the other floating) | Terminal B (The common combination of all like-named pins connected to terminal B) |
|----|---|---|
| 1. | All pins except V_{PS1} <u>3/</u> | All V_{PS1} pins |
| 2. | All input and output pins | All other input-output pins |

1/ Table II is restated in narrative form in 3.4 below.


2/ No connects are not to be tested.


3/ Repeat pin combination I for each named Power supply and for ground

(e.g., where V_{PS1} is V_{DD} , V_{CC} , V_{SS} , V_{BB} , GND, $+V_S$, $-V_S$, V_{REF} , etc).

3.4 Pin combinations to be tested.

- Each pin individually connected to terminal A with respect to the device ground pin(s) connected to terminal B. All pins except the one being tested and the ground pin(s) shall be open.
- Each pin individually connected to terminal A with respect to each different set of a combination of all named power supply pins (e.g., V_{SS1} , or V_{SS2} or V_{SS3} or V_{CC1} , or V_{CC2}) connected to terminal B. All pins except the one being tested and the power supply pin or set of pins shall be open.
- Each input and each output individually connected to terminal A with respect to a combination of all the other input and output pins connected to terminal B. All pins except the input or output pin being tested and the combination of all the other input and output pins shall be open.






▨ BONDABLE AREA

NOTE: CAVITY DOWN

| | | | | | |
|-------------------------|--------|------------|------|---|------|
| PKG. CODE: X5-1 | | SIGNATURES | DATE |  CONFIDENTIAL & PROPRIETARY | |
| CAV./PAD SIZE: 35x34 | PKG. | | | BOND DIAGRAM #: | REV: |
| | DESIGN | | | 05-3401-0001 | A |

ONCE PER SOCKET

ONCE PER BOARD



DEVICES: MAX 5464

MAX. EXPECTED CURRENT =270 uA

NOTES: