

RELIABILITY REPORT FOR MAX9768ETG+ PLASTIC ENCAPSULATED DEVICES

September 30, 2009

## MAXIM INTEGRATED PRODUCTS

120 SAN GABRIEL DR. SUNNYVALE, CA 94086

Approved by
Ken Wendel
Quality Assurance
Director, Reliability Engineering



#### Conclusion

The MAX9768ETG+ successfully meets the quality and reliability standards required of all Maxim products. In addition, Maxim's continuous reliability monitoring program ensures that all outgoing product will continue to meet Maxim's quality and reliability standards.

#### **Table of Contents**

- I. ......Device Description V. .....Quality Assurance Information
- II. ......Manufacturing Information
- III. ......Packaging Information
- .....Attachments

VI. ......Reliability Evaluation

- I. Device Description
  - A. General

The MAX9768 mono 10W Class D speaker amplifier provides high-quality, efficient audio power with an integrated volume control function. The MAX9768 features a 64-step dual-mode (analog or digitally programmable) volume control and mute function. The audio amplifier operates from a 4.5V to 14V single supply and can deliver up to 10W into an 8 speaker with a 14V supply. A selectable spread-spectrum mode reduces EMI-radiated emissions, allowing the device to pass EMC testing with ferrite bead filters and cable lengths up to 1m. The MAX9768 can be synchronized to an external clock, allowing synchronization of multiple Class D amplifiers. The MAX9768 features high 77dB PSRR, low 0.08% THD+N, and SNR up to 97dB. Robust short-circuit and thermal-overload protection prevent device damage during a fault condition. The MAX9768 is available in a 24-pin thin QFN-EP (4mm x 4mm x 0.8mm) package and is specified over the extended -40°C to +85°C temperature range.



II. Manufacturing Information

A. Description/Function: 10W Mono Class D Speaker Amplifier with Volume Control B. Process: S45 C. Number of Device Transistors:

7/27/2007

filler

- California, Texas or Japan China, Thailand, Malaysia
- F. Date of Initial Production:

D. Fabrication Location:

E. Assembly Location:

## III. Packaging Information

A. Package Type:	24-pin TQFN 4x4
B. Lead Frame:	Copper
C. Lead Finish:	100% matte Tin
D. Die Attach:	Conductive Epoxy
E. Bondwire:	Gold (1 mil dia.)
F. Mold Material:	Epoxy with silica fi
G. Assembly Diagram:	#05-9000-2049
H. Flammability Rating:	Class UL94-V0
I. Classification of Moisture Sensitivity per JEDEC standard J-STD-020-C	Level 1
J. Single Layer Theta Ja:	48°C/W
K. Single Layer Theta Jc:	2.7°C/W
L. Multi Layer Theta Ja:	36°C/W
M. Multi Layer Theta Jc:	2.7°C/W

#### IV. Die Information

A. Dimensions:	88 X 98 mils
B. Passivation:	Si <sub>3</sub> N <sub>4</sub> /SiO <sub>2</sub> (Silicon nitride/ Silicon dioxide)
C. Interconnect:	Al/0.5%Cu with Ti/TiN Barrier
D. Backside Metallization:	None
E. Minimum Metal Width:	Metal1 = 0.5 / Metal2 = 0.6 / Metal3 = 0.6 microns (as drawn)
F. Minimum Metal Spacing:	Metal1 = 0.45 / Metal2 = 0.5 / Metal3 = 0.6 microns (as drawn)
G. Bondpad Dimensions:	5 mil. Sq.
H. Isolation Dielectric:	SiO <sub>2</sub>
I. Die Separation Method:	Wafer Saw



#### V. Quality Assurance Information

A.	Quality Assurance Contacts:	Ken Wendel (Director, Reliability Engineering)		
		Bryan Preeshl (Managing Director of QA)		
В.	Outgoing Inspection Level:	0.1% for all electrical parameters guaranteed by the Datasheet.		
		0.1% For all Visual Defects.		
C.	Observed Outgoing Defect Rate:	< 50 ppm		
D.	Sampling Plan:	Mil-Std-105D		

## VI. Reliability Evaluation

A. Accelerated Life Test

The results of the 135°C biased (static) life test are shown in Table 1. Using these results, the Failure Rate (  $\lambda$ ) is calculated as follows:

 $\lambda = \underbrace{1}_{\text{MTTF}} = \underbrace{\frac{1.83}{192 \times 4340 \times 48 \times 2}}_{(\text{where } 4340 = \text{Temperature Acceleration factor assuming an activation energy of 0.8eV})$  $\lambda = 22.4 \times 10^{-9}$  $\lambda = 22.4 \text{ F.I.T. (60\% confidence level @ 25°C)}$ 

The following failure rate represents data collected from Maxim"s reliability monitor program. Maxim performs quarterly life test monitors on its processes. This data is published in the Reliability Report found at http://www.maxim-ic.com/qa/reliability/monitor. Cumulative monitor data for the S45 Process results in a FIT Rate of 0.49 @ 25C and 8.49 @ 55C (0.8 eV, 60% UCL)

## B. Moisture Resistance Tests

The industry standard 85°C/85%RH or HAST testing is monitored per device process once a quarter.

C. E.S.D. and Latch-Up Testing

The AU55 die type has been found to have all pins able to withstand a HBM transient pulse of +/-2500 V per JEDEC JESD22-A114. Latch-Up testing has shown that this device withstands a current of +/-250 mA.



# Table 1 Reliability Evaluation Test Results

#### MAX9768ETG+

TEST ITEM	TEST CONDITION	FAILURE IDENTIFICATION	SAMPLE SIZE	NUMBER OF FAILURES			
Static Life Test (Note 1)							
	Ta = 135°C	DC Parameters	48	0			
	Biased	& functionality					
	Time = 192 hrs.						
Moisture Testing (	Note 2)						
HAST	Ta = 130°C	DC Parameters	77	0			
	RH = 85%	& functionality					
	Biased						
	Time = 96hrs.						
Mechanical Stress (Note 2)							
Temperature	-65°C/150°C	DC Parameters	77	0			
Cycle	1000 Cycles	& functionality					
-	Method 1010						

Note 1: Life Test Data may represent plastic DIP qualification lots.

Note 2: Generic Package/Process data