

Maxim > Design Support > Technical Documents > Application Notes > Wireless and RF > APP 449

Keywords: REP, REP006, rapid engineering prototype, J-CDMA, JCDMA, japanese CDMA, PA, linear RF, power amplifier, PAE, efficiency, power added efficiency

APPLICATION NOTE 449

REP006: Linear RF Power Amplifier Matched for High Efficiency at Low Power

Nov 01, 2000

Abstract: Rapid Engineering Prototype (REP) #006 offers the MAX2269 linear power amplifier (PA) custom-tuned for Japanese cellular CDMA application. This PA offers 17% PAE at +16dBm in low-power mode. Contact the factory for a detailed report with the application circuit and measurement data.

Rapid Engineering Prototypes are real circuits that Maxim application engineers have built and measured in our labs. They can provide a starting point for new RF designs. They are not available as Evaluation Kits.

Additional Information:

- Wireless Product Line Page
- Quick View Data Sheet for the MAX2267/MAX2268/MAX2269
- Applications Technical Support



Click here for an overview of the wireless components used in a typical radio transceiver.



Objective: To develop and measure an external switch for maximizing power-added efficiency (PAE) with this Japanese dual-path cellular-band PA.

By using an external (off-chip) high/low power-amplifier switch, the MAX2269 dual-path power amplifier can be set up for highest PAE. Because a discrete external path switch can be made by means of a semiconductor process whose characteristics are optimized for switching, an on-chip switch would typically have slightly higher loss and poorer isolation (but the subsequent circuit costs less and is smaller). Here, the MAX2269 was tuned for efficiency using its low-power path, resulting in longest battery life. This is because use in metropolitan areas results in transmit power on an average of between -20dBm and -16dBm, and the high-powered amplifier path is required infrequently.

The MAX2269 linear RF power amplifier is designed for Japanese cellular-band CDMA, PDC, and IS-136-based TDMA modulation formats. For best low-power PAE, the MAX2269 offers a switched dualpath amplifier arrangement. Statistically, CDMA handsets operate most of the time in a low-powered path (around +16dBm output), which is where PAE needs to be optimized. Using an external FET switch or pin diode, the MAX2269 offers the industry's highest (17% typical) PAE in low-power mode.

Schematic of the MAX2269 Evaluation Kit (PDF, 47K)

Related Parts	
MAX2269	+2.7V, Single-Supply, Cellular-Band Linear Power Amplifiers

More Information

For Technical Support: http://www.maximintegrated.com/support For Samples: http://www.maximintegrated.com/samples Other Questions and Comments: http://www.maximintegrated.com/contact

Application Note 449: http://www.maximintegrated.com/an449 APPLICATION NOTE 449, AN449, AN 449, APP449, Appnote449, Appnote 449 Copyright © by Maxim Integrated Products Additional Legal Notices: http://www.maximintegrated.com/legal